



## **MYLAR® CKFPE - 400/600**

### **Product Description**

Mylar® CKFPE is a clear, formable, puncture resistant packaging film. It is designed for thermoformed dual-ovenable package structures.

### **General Product Info**

MYLAR® CKFPE can be formed to various draw depths depending on the mold shape. Heat over forming is required. Forming temperature and time will be dependent on process ambient conditions, but typically optimal forming temperature is 120°C and forming time is 2.0 seconds.

### **Typical Applications**

Typical applications include thermoformed, flexible packages where a capping web such MYLAR® CKP5E is heat sealed to the top of the formed sheet once the food product has been placed inside the package. MYLAR® CKFPE is designed to work with most roll stock thermoforming equipment.

Solutions to minimize contact with raw meat are increasingly necessary due to the heightened awareness of contamination. MYLAR® CKFPE, combined with a MYLAR® capping web, offers the ability to package raw meats, poultry, and seafood in lightweight, sealed containers that can go directly from the freezer into a microwave, convection or conventional home oven. Handling is minimized between the processing plant and the finished, ready-to-eat product. Using MYLAR® CKFPE, meat processors can enhance consumer value with portion control packs containing seasoned or marinated individual meat servings. All packages made with MYLAR® CKFPE self baste which enhances flavor and tenderness while significantly reducing cooking times. MYLAR® CKFPE provides convenience solutions for today's busy lifestyle and growing trends in healthy eating.

DuPont Teijin Films is unable to provide information about the shelf life of food product packaged in MYLAR® Cook films. Food quality, process conditions, and storage conditions play a key role in determining the shelf life of packaged foods. These conditions are many and outside of DuPont Teijin Films' control. DuPont Teijin Films makes no warranties, express or implied, and assumes no liability in connection with any use of this information.

### **Approvals**

**Food Contact Status** - MYLAR® CKFPE has been assessed against the European and the United States of America Food Contact legislation. Please contact your DuPont Teijin Film representative to receive the Regulatory Compliance documents, which give detailed information on individual country regulations, overall and specific migration limits and possible restrictions for specific applications.

## Disposal

Dispose of MYLAR® CKFPE does not present special disposal problems. It can be buried as a relatively inert material in a landfill or burned in an incinerator with normal refuse. The incinerator should have sufficient draft to exhaust all combustion products through the stack to avoid exposure to irritating fumes. The incinerator must be capable of scrubbing out acidic off gas. The disposal method should comply with local, state and federal regulations, in compliance with local and country regulations.

## Typical Properties

Available Thickness [Gauge]
400; 600

Property	Thickness	Value	Units	Test
<b>BARRIER</b>				
Gas Permeability - O <sub>2</sub> , 24 hr	400	0.96	cc/ 100in <sup>2</sup>	ASTM D3985 22° C/75% RH/1 ATM
Gas Permeability - O <sub>2</sub> , 24 hr	600	0.8	cc/ 100in <sup>2</sup>	ASTM D3985 22° C/75% RH/1 ATM
WVTR	400	0.59	g/100 in <sup>2</sup> /day	ASTM F1249 38°C, 90% RH
WVTR	600	0.51	g/100 in <sup>2</sup> /day	ASTM F1249 38°C, 90% RH
<b>OPTICAL</b>				
Haze	400	11	%	ASTM D1003
Haze	600	15	%	ASTM D1003
Total Light Transmission (TLT)	400- 600	90	%	ASTM D1003
<b>PHYSICAL</b>				
C.O.F. (dynamic) A-B	400	0.3	n/a	ASTM D1894 (untreated to treated)
C.O.F. (dynamic) A-B	600	0.3	n/a	ASTM D1894 (untreated to treated)
C.O.F. (static) A-B	400	0.5	n/a	ASTM D1894 (untreated to treated)
C.O.F. (static) A-B	600	0.4	n/a	ASTM D1894 (untreated to treated)
Elongation at Break MD	400	205	%	ASTM D882A
Elongation at Break MD	600	193	%	ASTM D882A
Elongation at Break TD	400	158	%	ASTM D882A
Elongation at Break TD	600	157	%	ASTM D882A
Tear Initiation MD	400	9	lbs	ASTM D1004

Tear Initiation MD	600	13	lbs	ASTM D1004
Tear Initiation TD	400	7	lbs	ASTM D1004
Tear Initiation TD	600	13	lbs	ASTM D1004
Tear Propagation MD	400	1.3	lbs	ASTM D1938
Tear Propagation MD	600	2.3	lbs	ASTM D1938
Tear Propagation TD	400	1.6	lbs	ASTM D1938
Tear Propagation TD	600	3.0	lbs	ASTM D1938
Tensile Strength MD (break)	400	10,278	psi	ASTM D882A
Tensile Strength MD (break)	600	13,086	psi	ASTM D882A
Tensile Strength TD (break)	400	10,237	psi	ASTM D882A
Tensile Strength TD (break)	600	11,099	psi	ASTM D882A
Yield (nominal)	400	5,329	in <sup>2</sup> /lb	
Yield (nominal)	600	3,713	in <sup>2</sup> /lb	

## Contact Info

DuPont Teijin Films U.S. Limited Partnership  
 3600 Discovery Drive  
 Chester, VA 23836 USA  
 Tel: (800) 635-4639  
 Fax: (804) 530-9867

## Disclaimer

Note: These values are typical performance data for DuPont Teijin Films' polyester film; they are not intended to be used as design data. We believe this information is the best currently available on the subject. It is offered as a possible helpful suggestion in experimentation you may care to undertake along these lines. It is subject to revision as additional knowledge and experience is gained. DuPont Teijin Films makes no guarantee of results and assumes no obligation or liability whatsoever in connection with this information. This publication is not a license to operate under, or intended to suggest infringement of, any existing patents.

CAUTION: Do not use in medical applications involving permanent implantation in the human body ([DuPont Teijin Films Medical Policy](#)). For other medical applications, see the [Medical Caution Statement](#). DuPont Teijin Films accepts no liability for use of its products in medical applications not reviewed and approved by DuPont Teijin Films or for product misuse. DuPont Teijin Films supplies products to an agreed specification and does not manufacture products designed specifically for medical end use.

Melinex®, Mylar® and Melinex® ST™ are registered trademarks of DuPont Teijin Films U.S. Limited Partnership. Teijin® and Teton® are registered trademarks of Teijin Limited used under license by DuPont Teijin Films U.S. Limited Partnership. Teonex® is a registered trademark of Teijin DuPont Films Japan Limited and is used under license by DuPont Teijin Films U.S. Limited Partnership.